


Long-Life Water-Resistant Bearing Grease for Rolling Mills




GREASE FOR SEALED TYPE ROLLER BEARINGS

What causes flaking and how can it be prevented?


Flaking occurs when small pieces of bearing material are split off from the smooth surface of the raceway or rolling elements due to rolling fatigue, thereby causing areas with rough and coarse texture.

Possible causes are due to poor lubrication, improper lubricant, entry of foreign debris and entry of water.

Particularly for the sealed type 4 rows taper roller bearings, NSK developed long-life water resistant grease (AQGRD R1) which is enhanced in base oil viscosity and special water-resistant additives.



Working condition of bearing for work roll




Benefits of water resistant grease technology

- › Inhibits water entry to rolling surface
- › Minimizes premature flaking and rust
- › More than doubled life with new grease

EXISTING GREASE VERSUS NEW GREASE

EXISTING GREASE




NEW GREASE (AQGRD R1)

Water resistant grease technology is:


› The ability to repel water with a thicker layer of oil film and the protective oxide film.

› In the case where there is insufficient lubrication, the protective oxide film is still able to prevent water contact between the roller and the surface.



Indirect contact to prevent flaking and rust resulting extension of bearing life


BASE OIL VISCOSITY



Conditions

Bearing: 32968, P/C: 0.15, Speed: 567 r/min

FLAKING LIFE TEST



Scenario of cold rolling work roll at following conditions

Bearing: HR32017XJ (open single-row tapered roller bearing)
 Room temperature while bearing temperature at 60-70 °C
 Radius force: 35.8kN, Axle force: 15.7kN, P/C: 0.25,
 Speed: 1500 r/min

TYPICAL ANALYSIS

CONTENTS	AQGRD R1
Color	Yellow
NLGI grade	2
Consistency (worked penetration)	322
Base oil	Mineral oil
Thickener	Lithium complex soap
Base oil viscosity, mm ² /s at 40°C/ at 100°C	352 / 28.7
Viscosity index	108
Dropping point (°C)	216
Oil separation (mass%)	1.4
Oxidation stability (kPa)	30
Water washout (mass%)	59
Corrosion preventive properties (based on ASTM D1743)	#1 (no corrosion)

AQGRD R1 grease is highly recommended for sealed type roller bearings to avoid wastage of the grease.



Worldwide Sales Offices

P: Phone ☆: Head Office

NSK LTD. HEADQUARTERS, TOKYO JAPAN

INDUSTRIAL MACHINERY BUSINESS DIVISION-HEADQUARTERS P: +81-3-3779-7227
 AUTOMOTIVE BUSINESS DIVISION-HEADQUARTERS P: +81-3-3779-7189

Africa

South Africa:

NSK SOUTH AFRICA (PTY) LTD.
 SANDTON P: +27-011-458-3600

Aisia and Oceania

Australia:

NSK AUSTRALIA PTY. LTD.
 MELBOURNE ☆ P: +61-3-9765-4400
 SYDNEY P: +61-2-9839-2300
 BRISBANE P: +61-7-3347-2600
 PERTH P: +61-8-9256-5000

New Zealand:

NSK NEW ZEALAND LTD.
 AUCKLAND P: +64-9-276-4992

China:

NSK (SHANGHAI) TRADING CO., LTD.
 JIANGSU ☆ P: +86-512-5796-3000

NSK (CHINA) INVESTMENT CO., LTD.

JIANGSU ☆ P: +86-512-5796-3000
 BEIJING P: +86-10-6590-8161
 TIAN JIN P: +86-22-8319-5030
 CHANGCHUN P: +86-431-8898-8682
 SHENYANG P: +86-24-2334-2868
 DALIAN P: +86-411-8800-8168
 NANJING P: +86-25-8472-6671
 FUZHOU P: +86-591-8380-1030
 WUHAN P: +86-27-8556-9630
 QINGDAO P: +86-532-5568-3877
 GUANGZHOU P: +86-20-3817-7800
 CHANGSHA P: +86-731-8571-3100
 LUOYANG P: +86-379-6069-6188
 XI'AN P: +86-29-8765-1896
 CHONGQING P: +86-23-6806-5310
 CHENGDU P: +86-28-8528-3680

NSK CHINA SALES CO., LTD.

JIANGSU ☆ P: +86-512-5796-3000

NSK HONG KONG LTD.

HONG KONG ☆ P: +852-2739-9933
 SHENZHEN P: +86-755-25904886

Taiwan:

TAIWAN NSK PRECISION CO., LTD.

TAIPEI ☆ P: +886-2-2772-3355
 TAICHUNG P: +886-4-2708-3393
 TAINAN P: +886-6-215-6058

India:

NSK BEARINGS INDIA PRIVATE LTD.

CHENNAI ☆ P: +91-44-2847-9600
 MUMBAI P: +91-22-2838-7787
 JAMSHEDPUR P: +91-657-2421144
 GURGAON P: +91-124-4838000

Indonesia:

PT. NSK INDONESIA
 JAKARTA P: +62-21-252-3458

Korea:

NSK KOREA CO., LTD.
 SEOUL P: +82-2-3287-0300

Malaysia:

NSK BEARINGS (MALAYSIA) SDN.BHD.
 SHAH ALAM ☆ P: +60-3-7803-8859
 PRAI P: +60-4-3902275
 JOHOR BAHRU P: +60-7-3546290
 IPOH P: +60-5-2555000

Philippines:

NSK REPRESENTATIVE OFFICE
 MANILA P: +63-2-893-9543

Singapore:

NSK INTERNATIONAL (SINGAPORE) PTE LTD.
 SINGAPORE P: +65-6496-8000

NSK SINGAPORE (PRIVATE) LTD.

SINGAPORE P: +65-6496-8000

Thailand:

NSK BEARINGS (THAILAND) CO., LTD.
 BANGKOK P: +66-2320-2555

Vietnam:

NSK VIETNAM CO., LTD.
 HANOI P: +84-24-3955-0159

NSK REPRESENTATIVE OFFICE

HO CHI MINH CITY P: +84-28-3822-7907

Europe

United Kingdom:

NSK EUROPE LTD. (EUROPEAN HEADQUARTERS)
 MAIDENHEAD P: +44-1628-509-800

NSK UK LTD.

NEWARK P: +44-1636-605-123

France:

NSK FRANCE S.A.S.
 PARIS P: +33-1-30-57-39-39

Germany:

NSK DEUTSCHLAND GMBH
 DUSSELDORF ☆ P: +49-2102-4810
 STUTTGART P: +49-711-79082-0
 WOLFSBURG P: +49-5361-27647-10

Italy:

NSK ITALIA S.P.A.
 MILANO P: +39-299-5191

Netherlands:

NSK EUROPEAN DISTRIBUTION CENTRE B.V.
 TILBURG P: +31-13-4647647

Poland:

NSK REPRESENTATIVE OFFICE
 WARSAW P: +48-22-645-1525

Russia:

NSK POLSKA SP. Z O.O.
 SAINT-PETERSBURG P: +7-812-332-5071

Spain:

NSK SPAIN S.A.
 BARCELONA P: +34-93-289-2763

Turkey:

NSK RULMANLARI ORTA DOGU TIC. LTD. STI.
 ISTANBUL P: +90-216-5000-675

United Arab Emirates:

NSK BEARINGS GULF TRADING CO.
 DUBAI P: +971-(0)4-804-8200

North and South America

United States of America:

NSK AMERICAS, INC. (AMERICAN HEADQUARTERS)
 ANN ARBOR P: +1-734-913-7500

NSK CORPORATION

ANN ARBOR P: +1-734-913-7500

NSK PRECISION AMERICA, INC.

FRANKLIN ☆ P: +1-317-738-5000
 SAN JOSE P: +1-408-944-9400

NSK LATIN AMERICA, INC.

MIAMI P: +1-305-477-0605

Canada:

NSK CANADA INC.
 TORONTO ☆ P: +1-905-890-0740
 MONTREAL P: +1-514-633-1220

Argentina:

NSK ARGENTINA SRL
 BUENOS AIRES P: +54-11-4704-5100

Brazil:

NSK BRASIL LTDA.
 SUZANO ☆ P: +55-11-4744-2500
 JOINVILLE P: +55-47-3422-2239

Peru:

NSK PERU S.A.C.
 LIMA P: +51-493-4385

Mexico:

NSK RODAMIENTOS MEXICANA, S.A. DE C.V.
 SILAO, GUANAJUATO P: +52-472-103-9400

<As of December 2019>

For the latest information, please refer to the NSK website.

www.nsk.com

NSK Ltd. has a basic policy not to export any products or technology designated as controlled items by export-related laws. When exporting the products in this brochure, the laws of the exporting country must be observed. Specifications are subject to change without notice and without any obligation on the part of the manufacturer. Every care has been taken to ensure the accuracy of the data contained in this brochure, but no liability can be accepted for any loss or damage suffered through errors or omissions. We will gratefully acknowledge any additions or corrections.

For more information about NSK products, please contact: _____

