

Optimized Long-Life Cylindrical Roller Bearings for Continuous Casting Machines



Bearings for Continuous Casting Machines


Bearings for Guide Rolls

Bearings used in the guide rolls of continuous casting machines are exposed to harsh conditions such as heavy load at ultra-low-speed in a hot and wet environment. High-performance bearings with longer life and higher reliability are desirable under such circumstances.





NSK has successfully developed innovative cylindrical rolling bearings through our extensive knowledge, decades of experience in production and in the steel industry, cutting-edge analysis technology, and an optimized design figure. Furthermore, these bearings feature improved handling performance that suits the required functions of guide rolls.


Cutaway View




Features









NSK installed one of these bearings for continuous casting machines at a customer site to perform a real-world test. They fulfilled all the specifications required and yielded good results for operation stability, earning high praise from the client.


Field Test


Bearing number: 160NUB40VC4


Boundary dimensions: ϕ d160 mm × ϕ D240 mm × B80mm

Basic load ratings Cr:765 (kN), Cor:1,360 (kN)

Continuous Casting Machine (for Heavy Plates)








Roll Segment Unit

Arrangement of

Top & Bottom Roll

Roll Arrangement



Axle Box Structure

Test Results




Test period: 9 months

Production amount: Approx. 1.0M tons Appearance: No abnormalities detected

(Possible for continuous use)

Bearing Number List



	Dimensions (mm)			Bearing No.	Basic Load Ratings (kN)	
[d	D	В		Cr	Cor
	120	180	60	120NUB40V	450	740
	130	200	69	130NUB40V	570	950
	140	210	69	140NUB40V	560	960
	150	225	75	150NUB40V	665	1160
	160	240	80	160NUB40V	765	1360

1 NSK NSK 2



Worldwide Sales Offices P: Phone ☆: Head Office

NSK LTD. HEADQUARTERS, TOKYO INDUSTRIAL MACHINERY BUSINESS DIVISION-HEADQUARTE		MUMBAI	P: +91-22-2838-7787	Spain: NSK SPAIN S.A.	
		Indonesia:			D 04 00 000 0700
AUTOMOTIVE BUSINESS DIVISION-HEADQUARTER	HS P: +81-3-3779-7189	PT. NSK INDONESIA	D 00 04 050 0450	BARCELONA	P: +34-93-289-2763
Africa		JAKARTA	P: +62-21-252-3458	Turkey:	
South Africa:		Korea:		NSK RULMANLARI ORTA DOGU 1	
NSK SOUTH AFRICA (PTY) LTD.		NSK KOREA CO., LTD.	D 00 0 0007 0000	ISTANBUL	P: +90-216-477-7111
SANDTON	P: +27-11-458-3600	SEOUL	P: +82-2-3287-0300	United Arab Emirates:	_
Aisia and Oceania		Malaysia:		NSK BEARINGS GULF TRADING (
Australia:		NSK BEARINGS (MALAYSIA) SDN		DUBAI	P: +971-4-804-8207
NSK AUSTRALIA PTY, LTD.		SHAH ALAM ☆	P: +60-3-7803-8859	North and South America	
MELBOURNE ☆	P: +61-3-9765-4400	PRAI	P: +60-4-3902275	United Sates of America:	
SYDNEY	P: +61-2-9839-2300	JOHOR BAHRU	P: +60-7-3546290	NSK AMERICAS, INC. (AMERICAN	I HEADQUARTERS)
BRISBANE	P: +61-7-3347-2600	IPOH	P: +60-5-2555000	ANN ARBOR	P: +1-734-913-7500
PERTH	P: +61-8-9256-5000	Philippines:		NSK CORPORATION	
	P: +61-6-9256-5000	NSK REPRESENTATIVE OFFICE		ANN ARBOR	P: +1-734-913-7500
New Zealand:		MANILA	P: +63-2-893-9543	NSK PRECISION AMERICA, INC.	1111101010101000
NSK NEW ZEALAND LTD.	D 04 0 070 4000	Singapore:		FRANKLIN &	P: +1-317-738-5000
AUCKLAND	P: +64-9-276-4992	NSK INTERNATIONAL (SINGAPO	RE) PTE LTD.	SAN JOSE	P: +1-408-944-9400
China:	_	SINGAPORE	P: +65-6496-8000	NSK LATIN AMERICA, INC.	1:+1-400-344-3400
NSK (SHANGHAI) TRADING CO., LTD		NSK SINGAPORE (PRIVATE) LTD		MIAMI	P: +1-305-477-0605
JIANGSU ☆	P: +86-512-5796-3000	SINGAPORE	P: +65-6496-8000	Canada:	F. +1-303-477-0003
NSK (CHINA) INVESTMENT CO., LTD		Thailand:		NSK CANADA INC.	
JIANGSU	P: +86-512-5796-3000	NSK BEARINGS (THAILAND) CO.	LTD		D 4 005 000 0740
BEIJING	P: +86-10-6590-8161	BANGKOK	P: +66-2320-2555	TORONTO ☆	P: +1-905-890-0740
TIAN JIN	P: +86-22-8319-5030	Vietnam:	1:+00 2020 2000	MONTREAL	P: +1-514-633-1220
CHANGCHUN	P: +86-431-8898-8682	NSK VIETNAM CO., LTD.		VANCOUVER	P: +1-877-994-6675
SHENYANG	P: +86-24-2334-2868	HANOI	P: +84-24-3955-0159	Argentina:	
DALIAN	P: +86-411-8800-8168	NSK REPRESENTATIVE OFFICE	P. +64-24-3935-0159	NSK ARGENTINA SRL	
NANJING	P: +86-25-8472-6671		P: +84-28-3822-7907	BUENOS AIRES	P: +54-11-4704-5100
FUZHOU	P: +86-591-8380-1030	HO CHI MINH CITY	P: +84-28-3822-7907	Brazil:	
WUHAN	P: +86-27-8556-9630	Europe		NSK BRASIL LTDA.	
QINGDAO	P: +86-532-5568-3877	United Kingdom:		SUZANO ☆	P: +55-11-4744-2500
GUANGZHOU	P: +86-20-3817-7800	NSK EUROPE LTD. (EUROPEAN I	HEADQUARTERS)	BELO HORIZONTE	P: +55-31-3274-2591
CHANGSHA	P: +86-731-8571-3100	MAIDENHEAD	P: +44-1628-509-800	JOINVILLE	P: +55-47-3422-2239
LUOYANG	P: +86-379-6069-6188	NSK UK LTD.		PORTO ALEGRE	P: +55-51-3346-7851
XI'AN	P: +86-29-8765-1896	NEWARK	P: +44-1636-605-123	RECIFE	P: +55-81-3326-3781
CHONGQING	P: +86-23-6806-5310	France:		Peru:	
CHENGDU	P: +86-28-8528-3680	NSK FRANCE S.A.S.		NSK PERU S.A.C.	
	P. +00-20-0020-0000	PARIS	P: +33-1-30-57-39-39	LIMA	P: +51-1-493-4385
NSK CHINA SALES CO., LTD.	D 00 540 5700 0000	Germany:		Mexico:	
JIANGSU	P: +86-512-5796-3000	NSK DEUTSCHLAND GMBH		NSK RODAMIENTOS MEXICANA,	SADECV
NSK HONG KONG LTD.		DUSSELDORF ☆	P: +49-2102-4810	MEXICO CITY ☆	P: +52-55-3682-2900
HONG KONG ☆	P: +852-2739-9933	STUTTGART	P: +49-711-79082-0	MONTERREY	P: +52-81-8000-7300
SHENZHEN	P: +86-755-25904886	WOLFSBURG	P: +49-5361-27647-10	WONTENNET	1. +32-61-6000-7300
Taiwan:		italy:	F. +49=3301=27047=10		
TAIWAN NSK PRECISION CO., LTD.		NSK ITALIA S.P.A.			
TAIPEI ☆	P: +886-2-2509-3305		D 00 000 5101		
TAICHUNG	P: +886-4-2708-3393	MILANO	P: +39-299-5191		
TAINAN	P: +886-6-505-5861	Netherlands:			
TAIWAN NSK TECHNOLOGY CO., LT		NSK EUROPEAN DISTRIBUTION			
TAIPEI ☆	P: +886-2-2509-3305	TILBURG	P: +31-13-4647647		
TAICHUNG	P: +886-4-2358-2945	Poland:			
TAINAN	P: +886-6-505-5861	NSK REPRESENTATIVE OFFICE			
India:		WARSAW	P: +48-22-645-1525		
NSK INDIA SALES CO.PVT.LTD.		Russia:			<as 2018="" february="" of=""></as>
CHENNAI ☆	P: +91-44-2847-9600	NSK POLSKA SP. Z O.O.		For the latest information, please	refer to the NSK website
DELHI	P: +91-124-4838000	SAINT-PETERSBURG	P: +7-812-332-5071	i or the latest information, please	TOTAL TO THE MOST WEDSILE
DLLI II	1 31-124-4000000				www.nsk.com

NSK Ltd. has a basic policy not to export any products or technology designated as controlled items by export-related laws. When exporting the products in this brochure, the laws of the exporting country must be observed. Specifications are subject to change without notice and without any obligation on the part of the manufacturer. Every care has been taken to ensure the accuracy of the data contained in this brochure, but no liability can be accepted for any loss or damage suffered through errors or omissions. We will gratefully acknowledge any additions or corrections.

For more information about NSK products, please contact: -

