

Long Life Sealed Spherical Roller Bearings for Conveyor Pulley in Mining Industry



BEARING SERIES DESIGNED FOR MINING MACHINERY

Spherical Roller Bearings with Detachable Seal (SSRB)

Durability and reliability are of paramount importance to bearings used in mining and quarrying conveyor applications, where failure can impact productivity of the entire operation. For the arduous and highly contaminated operating conditions that typically prevail, NSK has developed a spherical roller bearing with a detachable seal. These long-life bearings provide operators of conveyor systems the benefits of increased uptime and a higher degree of reliable performance.



PROVEN BENEFITS

- › NSK’s tough steel has longer service life in contaminated operating environments
- › High performance seal design, including characteristics to compensate for bearing misalignment
- › Removable seal permits measurement of internal clearance during installation
- › Easy, bolt-fastened installation of seal
- › Dimensionally interchangeable with conventional spherical roller bearings

Combining the tough steel material technology with an advanced and easy-to-install seal, NSK delivered a high capacity and high performing solution to contaminant-related bearing failures in conveyor applications.

NSK MATERIAL STRENGTH

Microstructure (Hard and fine-grained carbon nitrides by Tough technology)

Fine grained carbon nitrides

Tough Steel

Carburized Steel

High Hardness (Tough Steel > Carburized Steel)

Hard contaminant particle gets pressed between rolling element and raceway.

Dent left in raceway surface has raised edges that multiply stress levels and decrease fatigue life.


Tough Steel

Standard Steel

DESIGN FEATURES

1. Bearing Boundary Dimension

Sealed SRB has the same boundary dimension as the Standard SRB, therefore it is not necessary to change the structure around the bearing.



2. Special Bearing Material & Heat Treatment



- › NSK adopts tougher steel for the inner & outer ring in order to extend bearing life and to prevent wear on the raceway under poor and severe lubrication conditions.
- › High Cr value can be obtained featuring the life extending attribute of tough steel bearing material.

3. Seal Design

- › Integral garter spring ensures high sealing performance with ability to compensate for bearing misalignment.
- › Hydrogenated nitrile butadiene rubber is used for seal material tolerating up to operating temperature of 100°C.
- › Seal lip contacts on the bearing inner ring with easy, bolt-fastened installation of the removable seal holder to the bearing outer ring.
- › NSK supplies the SSRB without packed grease featuring the ability for the end user to select and pack their own grease.



Garter Seal



NSK SSRB Reference Number	Cr (kN)	Cor (kN)	d (mm)	D (mm)	B (mm)	Speed Limit (rpm)	NSK (Standard Reference Number)
HTF120SLE226AGDD2KE4C3	480	525	120	215	58	1050	(22224EAKE4C3)
HTF130SLE226AGDD2KE4C3	565	635	130	230	64	970	(22226EAKE4C3)
HTF140SLE226AGDD2KE4C3	680	765	140	250	68	890	(22228CAMKE4C3)
HTF150SLE226AGDD2KE4C3	780	895	150	270	73	820	(22230CAMKE4C3)
HTF160SLE226AGDD2KE4C3	900	1050	160	290	80	780	(22232CAMKE4C3)
HTF170SLE316AGDD2KE4C3	915	1230	170	280	88	770	(23134CAMKE4C3)
HTF180SLE316AGDD2KE4C3	1060	1400	180	300	96	720	(23136CAMKE4C3)
HTF190SLE316AGDD2KE4C3	1190	1540	190	320	104	670	(23138CAMKE4C3)
HTF200SLE316AGDD2KE4C3	1360	1790	200	340	112	630	(23140CAMKE4C3)
HTF220SLE316AGDD2KE4C3	1570	2140	220	370	120	580	(23144CAMKE4C3)
HTF240SLE316AGDD2KE4C3	1830	2470	240	400	128	540	(23148CAMKE4C3)
HTF260SLE316AGDD2KE4C3	2210	2980	260	440	144	490	(23152CAMKE4C3)
HTF280SLE316AGDD2KE4C3	2330	3300	280	460	146	460	(23156CAMKE4C3)
HTF300SLE316AGDD2KE4C3	2770	4000	300	500	160	430	(23160CAMKE4C3)
HTF320SLE316AGDD2KE4C3	3400	4850	320	540	176	400	(23164CAMKE4C3)
HTF340SLE316AGDD2KE4C3	3850	5450	340	580	190	370	(23168CAMKE4C3)
HTF360SLE316AGDD2KE4C3	3900	5600	360	600	192	360	(23172CAMKE4C3)
HTF380SLE316AGDD2KE4C3	4000	5850	380	620	194	350	(23176CAMKE4C3)
HTF400SLE316AGDD2KE4C3	4200	6300	400	650	200	330	(23180CAMKE4C3)
HTF420SLE316AGDD2KE4C3	5250	7700	420	700	224	310	(23184CAMKE4C3)
HTF440SLE316AGDD2KE4C3	5450	8200	440	720	226	300	(23188CAMKE4C3)
STF460SLE316AGDD2KE4C3	6050	9150	460	760	240	280	(23192CAMKE4C3)
STF480SLE316AGDD2KE4C3	6550	10100	480	790	248	270	(23196CAMKE4C3)

Worldwide Sales Offices

P: Phone ☆: Head Office

NSK LTD. HEADQUARTERS, TOKYO JAPAN

INDUSTRIAL MACHINERY BUSINESS DIVISION-HEADQUARTERS P: +81-3-3779-7227
AUTOMOTIVE BUSINESS DIVISION-HEADQUARTERS P: +81-3-3779-7189

Africa

South Africa:

NSK SOUTH AFRICA (PTY) LTD.

SANDTON P: +27-011-458-3600

Aisia and Oceania

Australia:

NSK AUSTRALIA PTY. LTD.

MELBOURNE ☆ P: +61-3-9765-4400
SYDNEY P: +61-2-9839-2300
BRISBANE P: +61-7-3347-2600
PERTH P: +61-8-9256-5000

New Zealand:

NSK NEW ZEALAND LTD.

AUCKLAND P: +64-9-276-4992

China:

NSK (SHANGHAI) TRADING CO., LTD.

JIANGSU ☆ P: +86-512-5796-3000

NSK (CHINA) INVESTMENT CO., LTD.

JIANGSU ☆ P: +86-512-5796-3000
BEIJING P: +86-10-6590-8161
TIAN JIN P: +86-22-8319-5030
CHANGCHUN P: +86-431-8898-8682
SHENYANG P: +86-24-2334-2868
DALIAN P: +86-411-8800-8168
NANJING P: +86-25-8472-6671
FUZHOU P: +86-591-8380-1030
WUHAN P: +86-27-8556-9630
QINGDAO P: +86-532-5568-3877
GUANGZHOU P: +86-20-3817-7800
CHANGSHA P: +86-731-8571-3100
LUOYANG P: +86-379-6069-6188
XI'AN P: +86-29-8765-1896
CHONGQING P: +86-23-6806-5310
CHENGDU P: +86-28-8528-3680

NSK CHINA SALES CO., LTD.

JIANGSU ☆ P: +86-512-5796-3000

NSK HONG KONG LTD.

HONG KONG ☆ P: +852-2739-9933
SHENZHEN P: +86-755-25904886

Taiwan:

TAIWAN NSK PRECISION CO., LTD.

TAIPEI ☆ P: +886-2-2772-3355
TAICHUNG P: +886-4-2708-3393
TAINAN P: +886-6-215-6058

India:

NSK BEARINGS INDIA PRIVATE LTD.

CHENNAI ☆ P: +91-44-2847-9600
MUMBAI P: +91-22-2838-7787
JAMSHEDPUR P: +91-657-2421144
GURGAON P: +91-124-4838000

Indonesia:

PT. NSK INDONESIA

JAKARTA P: +62-21-252-3458

Korea:

NSK KOREA CO., LTD.

SEOUL P: +82-2-3287-0300

Malaysia:

NSK BEARINGS (MALAYSIA) SDN.BHD.

SHAH ALAM ☆ P: +60-3-7803-8859
PRAI P: +60-4-3902275
JOHOR BAHRU P: +60-7-3546290
IPOH P: +60-5-2555000

Philippines:

NSK REPRESENTATIVE OFFICE

MANILA P: +63-2-893-9543

Singapore:

NSK INTERNATIONAL (SINGAPORE) PTE LTD.

SINGAPORE P: +65-6496-8000

NSK SINGAPORE (PRIVATE) LTD.

SINGAPORE P: +65-6496-8000

Thailand:

NSK BEARINGS (THAILAND) CO., LTD.

BANGKOK P: +66-2320-2555

Vietnam:

NSK VIETNAM CO., LTD.

HANOI P: +84-24-3955-0159

NSK REPRESENTATIVE OFFICE

HO CHI MINH CITY P: +84-28-3822-7907

Europe

United Kingdom:

NSK EUROPE LTD. (EUROPEAN HEADQUARTERS)

MAIDENHEAD P: +44-1628-509-800

NSK UK LTD.

NEWARK P: +44-1636-605-123

France:

NSK FRANCE S.A.S.

PARIS P: +33-1-30-57-39-39

Germany:

NSK DEUTSCHLAND GMBH

DUSSELDORF ☆ P: +49-2102-4810
STUTTGART P: +49-711-79082-0
WOLFSBURG P: +49-5361-27647-10

Italy:

NSK ITALIA S.P.A.

MILANO P: +39-299-5191

Netherlands:

NSK EUROPEAN DISTRIBUTION CENTRE B.V.

TILBURG P: +31-13-4647647

Poland:

NSK REPRESENTATIVE OFFICE

WARSAW P: +48-22-645-1525

Russia:

NSK POLSKA SP. Z O.O.

SAINT-PETERSBURG P: +7-812-332-5071

Spain:

NSK SPAIN S.A.

BARCELONA P: +34-93-289-2763

Turkey:

NSK RULMANLARI ORTA DOGU TIC. LTD. STI.

ISTANBUL P: +90-216-5000-675

United Arab Emirates:

NSK BEARINGS GULF TRADING CO.

DUBAI P: +971-(0)4-804-8200

North and South America

United States of America:

NSK AMERICAS, INC. (AMERICAN HEADQUARTERS)

ANN ARBOR P: +1-734-913-7500

NSK CORPORATION

ANN ARBOR P: +1-734-913-7500

NSK PRECISION AMERICA, INC.

FRANKLIN ☆ P: +1-317-738-5000

SAN JOSE P: +1-408-944-9400

NSK LATIN AMERICA, INC.

MIAMI P: +1-305-477-0605

Canada:

NSK CANADA INC.

TORONTO ☆ P: +1-905-890-0740

MONTREAL P: +1-514-633-1220

Argentina:

NSK ARGENTINA SRL

BUENOS AIRES P: +54-11-4704-5100

Brazil:

NSK BRASIL LTDA.

SUZANO ☆ P: +55-11-4744-2500

JOINVILLE P: +55-47-3422-2239

Peru:

NSK PERU S.A.C.

LIMA P: +51-493-4385

Mexico:

NSK RODAMIENTOS MEXICANA, S.A. DE C.V.

SILAO, GUANAJUATO P: +52-472-103-9400

<As of December 2019>

For the latest information, please refer to the NSK website.

www.nsk.com

NSK Ltd. has a basic policy not to export any products or technology designated as controlled items by export-related laws. When exporting the products in this brochure, the laws of the exporting country must be observed. Specifications are subject to change without notice and without any obligation on the part of the manufacturer. Every care has been taken to ensure the accuracy of the data contained in this brochure, but no liability can be accepted for any loss or damage suffered through errors or omissions. We will gratefully acknowledge any additions or corrections.

For more information about NSK products, please contact: _____

