


NSK Standard Ball Screws

High Speed SS Model

Quick
delivery

Blank
shaft end


NSK's high speed and low noise ball screws provide high-level performance for drive systems of industrial machines such as those used in manufacturing. A standard stock series assures quick delivery.




High Speed SS (HSS) Model Standard ball screws, high speed and low noise enable further performance improvements to be made.

The HMS and HMD Models, originally developed for machine tools, are an addition to NSK's lineup of standard ball screws. They have a wide range of applications, from general machines to high performance machines such as those requiring high speed and precision.

NSK's original recirculation system realized high speed and low noise. An optimum recirculation system has been adopted based on the lead.



SRC recirculation system is suitable for fine screw leads.



The end deflector and middle deflector recirculation system are suitable for medium leads.

High speed

Permissible rotational speed is more than double d·n limit value: high speed of 160 000

Low noise and vibrations

Noise level has been reduced by 50%: a reduction of 6 dB(A)
Vibration has been reduced drastically

Interchangeability

Installation dimensions are the same as those of a conventional SS Model

Compact


Compact design created using offset preload system

Convenience

Design flexibility has been improved by blank shaft end.
New support units are also provided for high speed operation.

High speed

The new recirculation system that utilizes NSK's high speed and low noise technology more than doubles the d·n value from 70 000 to 160 000. To extend the range of the lead to 20mm, high speed operation of over 60m/min. is possible.



- Allowable feed speed of combinations of shaft diameter and lead.


Shaft diameter [mm] \ Lead [mm]	5	10	12	16	20
32	25m/min	50m/min			
40		40m/min	48m/min	64m/min	80m/min
45		35m/min			
50		32m/min	38m/min		

*Allowable speed needs to be calculated. See the permissible rotational speed in the dimensions table.

Low noise and vibrations

Compared to our conventional products, the average noise level has been reduced by more than 6 dB(A), reducing the number of colliding balls and recirculation parts thanks to high speed, low noise technology.

The vibration level of the nut has also been reduced drastically.

**Interchangeability**

Installation dimensions are the same as those of a conventional SS Model

Compact

By improving the nut manufacturing technology, highly precise screw manufacturing is possible with the long nut.

Achieved high-level stiffness and high load capacity equivalent to that of double nut preload by changing the double nut preload to the offset preload of a single nut, and compact sized nut.

Seal

Adopted thin seals axially and shorten nut length

Convenience**Optional configurations are possible for ball screw length as well as for the shaft end design**

The blank shaft ends can be customized according to customers' requests. See page 11 in NSK's recommended design when drawing up plans for a shaft end. The support units are available on pages 12-14 in the case of NSK's recommended design.

New support unit: For high speeds and heavy loads

The support unit is applied for the thrust angular contact ball bearing, TAC series, with high precision and rigidity. NSK design is available attached to the support unit, which easily constitutes a system.


Oil supply

2 oil holes, M6×1.0, are provided in the nut flange periphery and the end of the nut flange.

A plug is standardly screwed into the periphery of the nut flange.

Ball screw specification

Accuracy grade	C5 of JIS B 1192 (1997)
Axial play Preload system	Axial play: 0 Offset preload (Z preload)
Thread direction	Right hand
Shaft end	Both shaft ends blank (Unhardened area: HRC 40 max.)



Reference No.

The reference number is an identification number or symbol used for each model.

Specify the reference number when ordering, and thereafter, specify the shape of the end of the shaft indicated by NSK.

Reference No. **HSS** **40** **10** **N1D** **0950**

High speed SS Model: HSS

Screw shaft diameter (mm)

Lead (mm)

Screw shaft length L_0 (mm)

NSK control number

Precautions

◆ Design

1. One end of the screw shaft is cut through.
2. If a ball screw of which the left shaft end (opposite the driving side) is the shape I. and if it is supported with the "fixed-fixed" supporting method, you should be aware that the operating life of support bearings may shorten due to thermal expansion of the screw shaft, depending on usage conditions. In this case, you should consider a structure that can accommodate thermal expansion of the screw shaft if necessary. Please consult with NSK for a detailed examination.
3. For general precautions concerning ball screws, please check NSK Catalog No.E3162 "Precision Machine Components".


◆ Usage

1. Instructions for shaft end processing

The high speed SS Model has a straight cut shaft end. Therefore, during actual use, the end of the shaft must be machined according to the customer's specifications. NSK recommends designated suppliers that offer quality assurances and precision guarantees. If any other supplier carries out processing, NSK will not provide a precision guarantee.


2. Service temperature environment of 60°C or less (at the nut outer temperature)
3. Only a rust preventive agent is applied at the time of delivery. Please apply lubricant, oil or grease before using.
4. The seals are installed on the end of the nut with the ball screw shaft. However, the ball screws should be provided with a dust cover to prevent debris such as dust and metal powder from entering.
5. If the nut accidentally comes off the screw shaft, please contact NSK.

Dimension: Lead 5, 10, and 12 Shaft screw dia.32, 40, 45 and 50



Reference No.	Screw shaft dia. d	Lead ℓ	Root dia. d_r	Effective balls turns \times Circuits	Basic load ratings [N]		Preload [N]	Dynamic friction torque, median [N·cm]	Nut rigidity [N/μm]	Ball nut dimensions									Screw shaft dimension				Lead accuracy			Run-out		Mass [kg]	Permissible rotational speed [min⁻¹]		Internal spatial volume of nut [cm³]							
					Dynamic C_d					Static C_{d0}		Diameter		Flange			Overall length		Bolt hole			Oil hole		Threaded length	Shaft end, right	Shaft end, left	Overall length	Travel compensation T	Deviation e_p	Variation V_u	Shaft straightness I	Radial run-out J	K					
					D_1	D_2	A	G	H	B	L _n	W	X	Y	Z	Q	L _t	d_2	L_2	d_3	L_3	L_o																
HSS3205N1D0650	32	5	29.2	2.5×2	21 800	56 000	920	17.0	840	57	58	85	32	42	13	89	71	6.6	11	6.5	8	400	32	200	29.2	50	650	-0.010	0.025	0.020	0.055	0.019	0.013	10	5.2	5 000	5 000	
HSS3205N1D0950																	600	250	100	950	-0.014	0.030	0.023	0.065				7.0	5 000	5 000								
HSS3205N1D1250																	900	250	100	1 250	-0.022	0.040	0.027	0.080				8.7	5 000	5 000								
HSS3205N1D1550																	1 150	300	100	1 550	-0.028	0.046	0.030	0.100				10.5	3 500	4 700								
HSS3205N1D1850																	1 450	300	100	1 850	-0.035	0.054	0.035	0.130				12.2	2 200	2 900								
HSS3210N1D0850	32	10	26.4	2.5×2	54 500	110 000	2 310	59.5	920	73	74	108	41	53.5	15	160	90	9	14	8.5	10	500	32	250	26.4	100	850	-0.012	0.027	0.020	0.065	0.019	0.013	43	8.9	5 000	5 000	
HSS3210N1D1050																	700	250	100	1 050	-0.017	0.035	0.025	0.080				10.0	5 000	5 000								
HSS3210N1D1450																	1 050	300	100	1 450	-0.025	0.046	0.030	0.100				12.2	4 100	5 000								
HSS3210N1D1850																	1 450	300	100	1 850	-0.035	0.054	0.035	0.130				14.3	2 100	2 800								
HSS3210N1D2250																	1 850	300	100	2 250	-0.045	0.065	0.040	0.170				16.5	1 200	1 700								
HSS4010N1D0950	40	10	34.4	2.5×2	61 200	137 000	2 600	74.5	1 090	81	82	124	47	61.5	18	163	102	11	17.5	11	12	600	40	250	34.4	100	950	-0.014	0.030	0.023	0.050	0.025	0.015	52	13.5	4 000	4 000	
HSS4010N1D1450																	1 050	300	100	1 450	-0.025	0.046	0.030	0.070				17.9	4 000	4 000								
HSS4010N1D2100																	1 600	350	150	2 100	-0.039	0.054	0.035	0.110				23.5	2 200	3 000								
HSS4012N1D1450		12	34.1	2.5×2	71 700	154 000	3 050	96.0	1 110	85	86	128	48	63.5	18	187	106	11	17.5	11	12	1 050	40	300	34.1	100	1 450	-0.025	0.046	0.030	0.070	0.025	0.015	67	19.1	4 000	4 000	
HSS4012N1D2100																	1 600	350	150	2 100	-0.039	0.054	0.035	0.110				24.8	2 200	3 000								
HSS4012N1D2900																	2 400	350	150	2 900	-0.058	0.077	0.046	0.140				31.8	900	1 300								
HSS4510N1D1450	45	10	39.4	2.5×2	65 800	157 000	2 710	82.0	1 210	87	88	132	50	65.5	18	163	110	11	17.5	11	12	1 050	45	300	39.4	100	1 450	-0.025	0.046	0.030	0.070	0.025	0.015	58	22.0	3 500	3 500	
HSS4510N1D2100																	1 600	350	150	2 100	-0.039	0.054	0.035	0.110				29.2	2 500	3 400								
HSS4510N1D2900																	2 400	350	150	2 900	-0.058	0.077	0.046	0.140				38.2	1 100	1 500								
HSS5010N1D1450		10	44.4	2.5×2	68 100	174 000	2 880	92.0	1 320	92	93	135	51	67	18	163	113	11	17.5	11	12	1 050	50	300	44.4	100	1 450	-0.025	0.046	0.030	0.070	0.025	0.015	64	26.3	3		

Dimension: Lead16, 20 Shaft screw dia.40



Reference No.	Screw shaft dia. d	Lead ℓ	Root dia. d_r	Effective balls turns \times Circuits	Basic load ratings [N]		Preload [N]	Dynamic friction torque, median [N·cm]	Nut rigidity [N/μm]	Ball nut dimensions								Screw shaft dimension				Lead accuracy			Run-out		Mass [kg]	Permissible rotational speed [min⁻¹]	Internal spatial volume of nut [cm³]						
					Dynamic C_d	Static C_{d0}				Diameter		Flange			Overall length	Bolt hole			Oil hole	Threaded length	Shaft end, right		Shaft end, left		Overall length	Travel compensation T	Deviation e_p	Variation V_u	Shaft straightness I	Radial run-out J	Run-out K				
					Diameter		D_1	D_2	A	G	H	B	L_n	W	X	Y	Z	Q	L_t	d_2	L_2	d_3	L_3	L_o											
					D_1	D_2	A	G	H	B	L_n	W	X	Y	Z	Q	L_t	d_2	L_2	d_3	L_3	L_o													
HSS4016N1D1450	40	16	34.1	3.7x1	66 900	131 000	2 850	104.0	970	85	86	128	48	63.5	18	160	106	11	17.5	11	11	1 050	300	100	1 450	-0.025	0.046	0.030	0.070	0.025	0.015	19.2	4 000	4 000	40
HSS4016N1D2100																			1 600	34.1	150	2 100	-0.039	0.054	0.035	0.110	25.0	2 200	3 000						
HSS4016N1D2900																			2 400		150	2 900	-0.058	0.077	0.046	0.140	32.2	900	1 300						
HSS4020N1D1450		20	34.1	3.7x1	66 500	131 000	2 850	116.5	960	85	86	128	48	63.5	18	192	106	11	17.5	11	11	1 050	300	100	1 450	-0.025	0.046	0.030	0.070	0.025	0.015	20.3	4 000	4 000	47
HSS4020N1D2100																			1 600	34.1	150	2 100	-0.039	0.054	0.035	0.110	26.2	2 200	3 000						
HSS4020N1D2900																			2 400		150	2 900	-0.058	0.077	0.046	0.140	33.5	900	1 300						

Notes: ● NSK support units are recommended. Refer to Page 12 to 14 for details.

● Only a rust preventive agent is applied at the time of delivery. Please apply lubricant, oil or grease before use.


● Nut rigidity: Values in the table are theoretical values obtained from the elastic deformation between ball grooves with preload and balls.

● Permissible rotational speed: Calculated values obtained from the critical speed between the threaded length and NSK's recommended shaft end design.

● *1: Unhardened area: HRC 40 max.

● *2: Imperfect hardened areas for one lead exists on both ends of a screw. Exercise care when stroke setting

Dimension: Recommendation for shaft end design



For drive side: Recommendation for shaft end design

Screw shaft diameter	Bearing installation		Thread screw		Support unit	Parts installation		Shaft length			
	Diameter	Length	Screw size	Length		Diameter	Length	Screw length	Shaft overall length	Shaft end hexagon hole	
	d	d ₁	L ₁	m ₁		d ₃	L ₃	L _t	L _o	B	h
32	25	89	M25×1.5	26	WBK25DF-31H WBK25DFD-31H	20	51	max 1 850	max 2 250	8 ^{+0.2} ₀	10
		104									
40	30	89	M30×1.5	26	WBK30DF-31H WBK30DFD-31H	25	61	max 2 400	max 2 900	10 ^{+0.2} ₀	12
		104									
45	35	92	M35×1.5	30	WBK35DF-31H WBK35DFD-31H WBK35DFF-31H	30	63	max 2 400	max 2 900	12 ^{+0.3} ₀	14
		107									
		122									
50	40	92	M40×1.5	30	WBK40DF-31H WBK40DFD-31H WBK40DFF-31H	35	78	max 2 400	max 2 900	14 ^{+0.3} ₀	18
		107									
		122									

For side opposite to drive side: Recommendation for shaft end design

Screw shaft diameter	Shape	Bearing installation		Thread screw		Snap ring ditch			Support unit (Bearing model)
		Diameter	Length	Screw size	Length	Width	Ditch diameter	Ditch location	
		d ₂	L ₂	m ₂	mL ₂	n	d _n	nL (xL)	
32	I	*				-	-	-	*
	II	25	20	-	-	1.35 ^{+0.14} ₀	23.9 ⁰ _{-0.21}	16.35 (5)	(6205)
40	I	*				-	-	-	*
	II	30	22	-	-	1.75 ^{+0.14} ₀	28.6 ⁰ _{-0.21}	17.75 (6)	(6206)
45	I	*				-	-	-	*
	II	35	23	-	-	1.75 ^{+0.14} ₀	33 ⁰ _{-0.25}	18.75 (6)	(6207)
50	I	*				-	-	-	*
	II	40	25	-	-	1.95 ^{+0.14} ₀	38 ⁰ _{-0.25}	19.95 (7)	(6208)


- Notes: ● The dimensions of the drawing can be flexibly set within limits.
 ● The support unit is available with a recommended design.
 ● *: The same as that of the drive side.

New support unit (For high speed and heavy load)





Heat generation has been reduced via adoption of a low preload type bearing. Along with speedup of the ball screw, permissible rotational speed have been improved.

The new support units are assembled with the thrust angular contact ball bearings, TAC series, which are a high precision, high rigidity, high speed type with the most suitable function and structure. The bearing combination comes in three types as shown in the figure below



Support unit reference No.



Dimension: Support unit


Reference No.	Support unit												Basic dynamic load rating [N]	Permissible axial load	Preload	Axial rigidity	Maximum starting torque	Lock nut					Bearing seat for unit			Permissible rotational speed	Mass
	d	D	D_1	D_2	L	L_1	L_2	A	W	d_i^*	V^*	M					H	D_3	L_3	[N·cm]	d	L_4	L_5	[min ⁻¹]	[kg]		
WBK25DF-31H	25	85	130	90	66	33	18	100	110	57	70	29 900	40 500	2 280	850	21	M25×1.5	41	45	20	8 500	25	89	26	5 200	3.1	
WBK25DFD-31H					81	48						48 500 (29 900)	81 500 (40 500)	3 100	1 250	28							104			3.4	
WBK30DF-31H	30	85	130	90	66	33	18	100	110	57	70	30 500	43 000	2 400	890	23	M30×1.5	46	50	20	10 100	30	89	26	4 900	3.0	
WBK30DFD-31H					81	48						50 000 (30 500)	86 000 (43 000)	3 260	1 310	30							104			3.3	
WBK35DF-31H	35	95	142	102	66	33	18	106	121	69	80	32 500	50 000	2 750	1 030	27	M35×1.5	50	55	22	13 800	35	92	30	4 100	3.4	
WBK35DFD-31H					81	48						53 000 (32 500)	100 000 (50 000)	3 740	1 500	34							107			4.3	
WBK35DFF-31H					96	48						53 000	100 000	5 490	2 060	43							122			5.0	
WBK40DF-31H	40	95	142	102	66	33	18	106	121	69	80	33 500	52 000	2 860	1 080	28	M40×1.5	55	60	22	15 500	40	92	30	4 100	3.6	
WBK40DFD-31H					81	48						54 000 (33 500)	104 000 (52 000)	3 900	1 590	36							107			4.2	
WBK40DFF-31H					96	48						54 000	104 000	5 730	2 150	46							122			4.7	

Notes:

- Rigidity: Values in the table are theoretical and obtained from the elastic deformation between ball groove and balls.
- Starting torque indicates torque due to the preload of the bearing. It does not include seal torque.
- $h5$ class of the fits tolerance is recommended.
- Pilot diameter and tapped screws marked with "*", are used for seal unit installation for NSK standard hollow shaft ball screws. They can also be used for the dust cover and damper installation.
- Grease is packed into bearings. It is not necessary to apply grease before use.
- Installation torque of a set screw 490[N·cm] (Reference value)
- The locknut has been designed to stay fastened, but it may come loose if a machine has strong vibrations. Apply construction adhesive as necessary.
- Allowable axial load is 0.7 times of the permissible axial load in the dimension table.
- Values in parentheses of basic dynamic load rating and permissible axial load are the values when axial load is applied in a line.
- Contact NSK if the rotational speed is 50 min⁻¹ and below.

Parts list

Parts No.	Part Name	Quantity
①	Housing	1
②	Retaining Cover	1
③	High accuracy thrust angular contact ball bearing	One set
④	Dust seal	2
⑤	Collar	2
⑥	Preload bolt	6 or 8
⑦	Shim	One set
⑧	Lock nut	1

- NSK support units are precisely preloaded and adjusted. Do not disassemble components ①, ②, ③, ④, ⑥ or ⑦.
- Lock nut ⑧ has been exclusively prepared for ball screws. The end surface of the nut is positioned precisely perpendicular to the V thread. Secure the lock nut using a set screw.

Worldwide Sales Offices

P: Phone ★: Head Office

NSK LTD. HEADQUARTERS, TOKYO JAPAN INDUSTRIAL MACHINERY BUSINESS DIVISION-HEADQUARTERS P: +81-3-3779-7227 AUTOMOTIVE BUSINESS DIVISION-HEADQUARTERS P: +81-3-3779-7189	Indonesia: PT. NSK INDONESIA JAKARTA P: +62-21-252-3458	Turkey: NSK RULMANLARI ORTA DOGU TIC. LTD. STI. ISTANBUL P: +90-216-5000-675
Africa South Africa: NSK SOUTH AFRICA (PTY) LTD. SANDTON P: +27-011-458-3600	Korea: NSK KOREA CO., LTD. SEOUL P: +82-2-3287-0300	United Arab Emirates: NSK BEARINGS GULF TRADING CO. DUBAI P: +971-(0)4-804-8200
Asia and Oceania Australia: NSK AUSTRALIA PTY. LTD. MELBOURNE ★ P: +61-3-9765-4400 SYDNEY P: +61-2-9839-2300 BRISBANE P: +61-7-3347-2600 PERTH P: +61-8-9256-5000	Malaysia: NSK BEARINGS (MALAYSIA) SDN.BHD. SHAH ALAM ★ P: +60-3-7803-8859 PRAI P: +60-4-3902275 JOHOR BAHRU P: +60-7-3546290 IPOH P: +60-5-2555000	North and South America United States of America: NSK AMERICAS, INC. (AMERICAN HEADQUARTERS) ANN ARBOR P: +1-734-913-7500
New Zealand: NSK NEW ZEALAND LTD. AUCKLAND P: +64-9-276-4992	Philippines: NSK REPRESENTATIVE OFFICE MANILA P: +63-2-893-9543	NSK CORPORATION ANN ARBOR P: +1-734-913-7500
China: NSK (SHANGHAI) TRADING CO., LTD. JIANGSU ★ P: +86-512-5796-3000	Singapore: NSK INTERNATIONAL (SINGAPORE) PTE LTD. SINGAPORE P: +65-6496-8000	NSK PRECISION AMERICA, INC. FRANKLIN ★ P: +1-317-738-5000 SAN JOSE P: +1-408-944-9400
NSK (CHINA) INVESTMENT CO., LTD. JIANGSU ★ P: +86-512-5796-3000 BEIJING P: +86-10-6590-8161 TIAN JIN P: +86-22-8319-5030 CHANGCHUN P: +86-431-8898-8682 SHENYANG P: +86-24-2550-5017 DALIAN P: +86-411-8800-8168 NANJING P: +86-25-8472-6671 FUZHOU P: +86-591-8380-1030 WUHAN P: +86-27-8556-9630 QINGDAO P: +86-532-5568-3877 GUANGZHOU P: +86-20-3817-7800 CHANGSHA P: +86-731-8571-3100 LUOYANG P: +86-379-6069-6188 XI'AN P: +86-29-8765-1896 CHONGQING P: +86-23-6806-5310 CHENGDU P: +86-28-8528-3680	Thailand: NSK BEARINGS (THAILAND) CO., LTD. BANGKOK P: +66-2320-2555	NSK LATIN AMERICA, INC. MIAMI P: +1-305-477-0605
Taiwan: TAIWAN NSK PRECISION CO., LTD. TAIPEI ★ P: +886-2-2772-3355 TAICHUNG P: +886-4-2708-3393 TAINAN P: +886-6-215-6058	Vietnam: NSK VIETNAM CO., LTD. HANOI P: +84-24-3955-0159	Canada: NSK CANADA INC. TORONTO ★ P: +1-888-603-7667 MONTREAL P: +1-514-633-1220
India: NSK BEARINGS INDIA PRIVATE LTD. CHENNAI ★ P: +91-44-28479600 GURGAON P: +91-124-4838000 MUMBAI P: +91-22-28387787 JAMSHEDPUR P: +91-657-2421144	Europe: NSK EUROPE LTD. (EUROPEAN HEADQUARTERS) MAIDENHEAD P: +44-1628-509-800	Argentina: NSK ARGENTINA SRL BUENOS AIRES P: +54-11-4704-5100
	NSK UK LTD. NEWARK P: +44-1636-605-123	Brazil: NSK BRASIL LTDA. SUZANO ★ P: +55-11-4744-2500 JOINVILLE P: +55-47-3422-2239
	France: NSK FRANCE S.A.S. PARIS P: +33-1-30-57-39-39	Peru: NSK PERU S.A.C. LIMA P: +51-493-4385
	Germany: NSK DEUTSCHLAND GMBH DUSSELDORF ★ P: +49-2102-4810 STUTTGART P: +49-711-79082-0 WOLFSBURG P: +49-5361-27647-10	Mexico: NSK RODAMIENTOS MEXICANA, S.A. DE C.V. SILAO, GUANAJUATO P: +52-472-500-9500
	Italy: NSK ITALIA S.P.A. MILANO P: +39-299-5191	
	Netherlands: NSK EUROPEAN DISTRIBUTION CENTRE B.V. TILBURG P: +31-13-4647647	
	Poland: NSK POLSKA SP.Z O.O. WARSAW P: +48-22-645-1525	
	Spain: NSK SPAIN S.A. BARCELONA P: +34-93-289-2763	

<As of July 2022>

For the latest information, please refer to the NSK website.

www.nsk.com

Every care has been taken to ensure the accuracy of data in this publication, but NSK Ltd. accepts no liability for any loss or damage incurred from errors or omissions. As we pursue continuous improvement, all content (text, images, product appearances, specifications, etc.) contained in this publication is subject to change without notice. Unauthorized copying and/or use of the contents of this publication is strictly prohibited.

Please investigate and follow the latest product export laws, regulations, and permit procedures when exporting to other countries.

For more information about NSK products, please contact:

